

# Reciprocating Pail Shaker

## DM-05RPS Series - 5 Gal. Electric or Pneumatic Shakers

Model No. DM-05RPS/115  
Electric Pail Shaker



### Benefits & Features

- Right-side up, upside down or horizontally
- Mix 1 or 2 gal cans, carton of 4x 1 gal. cans
- Pail holder will rotate through 360 degrees
- Locks in any position for shaking operation
- Positive action clamp will not loosen
- Factory prelubricated bearings throughout
- Virtually maintenance free
- Time proven eccentric drive last for years
- Explosion proof motor and switch
- 0-30 minute timer operation is optional
- 1 year warranty against defects/workmanship

### Specifications

1/3 Hp, 115/230 volts, 60 Hz, 1-phase, explosion proof motor and timer 10 ft., three wire cord or pneumatic motor. Dimensions, 33" long x 19" wide x 30" height. Shipping weight: 215 lbs.

### Operating Instructions

#### Full operation in a matter of seconds

1. Best shaker stability when mounted onto floor with lag bolts.
2. Cans should be loaded in upright position.
3. Bottom end clamp is recessed to prevent slippage.
4. Top clamp is then tightened using screw handle provided.
5. The cradle rotates and locks into upside down position.
6. Unit shakes aggressively to restore product uniformity.
7. Mixing is best accomplished in a nearly horizontal position.
8. Set a 4" block under 1 gal. cans & cartons to center load.
9. To change position, release pressure off clamping plates.
10. Lift end of locking lever at top of shaker.
11. Rotate cradle to desired position and re-set locking lever.
12. Set timer for required time, or flip switch for manual mixing.



For best batch mixing Quality Control before pumping, ask for DRUM-MATES® TQMixing™ Guidelines.  
NOTE: For easy "Pick 'n' Match", all mixer and pump drives and components are sold separately.  
DRUM-MATES® Inc., Mixer & Pump Div., Tel: 1-800-621-3786 and 609-261-1033, Fax: 609-261-1034